

Distribution board

# GTA 342-KT-t



## GTA 342-KT-t

**Distribution board**

**CUSTOMIZABLE**

Productnumber: 01634201

Dimensions: 320 x 440 x 179 mm

Module enclosure - Industrial Quality -, 3-row, PE/N terminal, with each 2 clamping points 16 mm<sup>2</sup>, 10 clamping points 6 mm<sup>2</sup>, masking and labelling strips, 3 x enclosure connectors (GGV)

**with transparent hinged door**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Protection class:	II
Type of protection:	IP65
vented:	no
Number of rows:	3
Number of modules:	42
Number of modules per row:	14
UL Type Rating:	3R

### Colours

Base unit colour:	grey
Cover colour:	transparent

### Dimensions

Width:	320 mm
Length:	440 mm
Height:	179 mm
Inner height:	157 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Surface mounting
Impact strength:	IK08

### mechanical properties

Sealable:	yes
Cover screw torque:	2.5 Nm
Flange variant:	yes
Stackable:	yes

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

### Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

## Accessories

[07251301 - GFS 13-m - Flange set](#)