

Meter housing

## GTZ 3-t



### GTZ 3-t

**Meter housing**

**CUSTOMIZABLE**

Productnumber: 02000301

Dimensions: 320 x 440 x 179 mm

Meter housing - Industrial Quality -, standard version sealable, with meter base plate and fastening screws, for mechanical electricity meters (induction meters), for electronic domestic supply meter with BKE-A adapter, 3 x enclosure connectors (GGV)

**with transparent cover**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Protection class:	II
Type of protection:	IP65
UL Type Rating:	3R

### Dimensions

Width:	320 mm
Length:	440 mm
Height:	179 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Surface mounting
Impact strength:	IK08
Cover screw torque:	2.5 Nm
Stackable:	yes

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

### Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

### Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

## Accessories

[07251301 - GFS 13-m - Flange set](#)