

NH fuse enclosure

## GST 2015-250



### GST 2015-250

NH fuse enclosure

CUSTOMIZABLE

Productnumber: 04601501

Dimensions: 320 x 320 x 179 mm

busbar enclosure - Industrial Quality -, equipped with 1 x NH 00-fuse-switch-disconnector, clip terminal clamp 1.5 - 50 mm<sup>2</sup>, Universal output, 5-pole busbar, with 5 busbar terminals for direct connection of a cable to the busbar system, additional N and PE terminal for each switch, 3 x enclosure connectors (GGV)

**busbar system 250 A, with transparent cover**



## Technical Data

### electrical characteristics

Rated operating voltage AC:	690 V
Protection class:	II
Type of protection:	IP65
Rated current:	250 A
UL Type Rating:	3R

### Dimensions

Width:	320 mm
Length:	320 mm
Height:	179 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Impact strength:	IK08
Cover screw torque:	2.5 Nm
Stackable:	yes

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

## Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

## Accessories

[07251201 - GFS 12-m - Flange set](#)

[07505601 - GSV 56 - Busbar connector](#)

[07673001 - KPK NH00 - Prism terminal](#)

[07675001 - KSR NH 00 - Terminal screws](#)