


NH fuse enclosure

## GST 5035-250 Plus



### GST 5035-250 Plus

NH fuse enclosure

CUSTOMIZABLE

Productnumber: 04753501

Dimensions: 640 x 440 x 179 mm

NH bus-mounting fuse empty enclosure for switchgear with additional connection space - Industrial Quality -, 3 x NH 00 fuse switch disconnecter enclosure, Rated current 125 A, Clamp connection 1.5 - 70 mm<sup>2</sup>, Output on top, on 5-pole busbar, with 5 busbar terminals 16 - 70 mm<sup>2</sup>, N terminal 4 - 35 mm<sup>2</sup>, PE terminal 4 - 35 mm<sup>2</sup>, 4 x enclosure connectors (GGV)

on busbar system 250 A, with transparent cover

IP65

IK08



690V

AC



## Technical Data

### electrical characteristics

Rated operating voltage AC:	690 V
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Protection class:	II
Type of protection:	IP65
UL Type Rating:	3R

### Dimensions

Width:	640 mm
Length:	440 mm
Height:	179 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Impact strength:	IK08
Cover screw torque:	2.5 Nm
Stackable:	yes

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

### Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

### Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

## Accessories

[07675001 - KSR NH 00 - Terminal screws](#)