

Flange

GFL 211-m

GFL 211-m

Flange

Productnumber: 07221101

Dimensions: 175 x 119 x 15 mm

Flange with metric knockouts, 2 x flange connectors (GFV)

Pre-stamped for cable insertion: 3x M32/25, 3x M20

IP65



Technical Data

electrical characteristics

Type of protection:	IP65
UL Type Rating:	3R

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	175 mm
Length:	119 mm
Height:	15 mm

Material characteristics

UV-resistant:	yes
Industry quality:	yes

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Polycarbonate, glass-fibre reinforced
---------------------	---------------------------------------