

Flange

GFL 30

GFL 30

Flange

Productnumber: 07230001

Dimensions: 275 x 119 x 15 mm

Flange, Smooth, 2 x flange connectors (GFV)



IP65

Technical Data

electrical characteristics

Type of protection:	IP65
UL Type Rating:	3R

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	275 mm
Length:	119 mm
Height:	15 mm

Material characteristics

UV-resistant:	yes
Industry quality:	yes

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Polycarbonate, glass-fibre reinforced
---------------------	---------------------------------------