

Flange

## GFL 390-m

### GFL 390-m

#### Flange

Productnumber: 07239001

Dimensions: 275 x 15 x 119 mm

Flange "metric" equipped, 2 x flange connectors (GFV)

**equipped with 42 x DMS M16**

IP65



---

## Technical Data

### electrical characteristics

|                     |               |
|---------------------|---------------|
| Type of protection: | IP65          |
| UL Type Rating:     | not specified |

### Colours

|                   |            |
|-------------------|------------|
| Accessory colour: | light grey |
|-------------------|------------|

### Dimensions

|         |        |
|---------|--------|
| Width:  | 275 mm |
| Length: | 15 mm  |
| Height: | 119 mm |

### Material characteristics

|                   |     |
|-------------------|-----|
| UV-resistant:     | no  |
| Industry quality: | yes |

### mechanical properties

|                       |    |
|-----------------------|----|
| with cable restraint: | no |
|-----------------------|----|

### Ambient conditions

|                        |                         |
|------------------------|-------------------------|
| Installation location: | protected outdoor areas |
|------------------------|-------------------------|

### Material

|                     |                                       |
|---------------------|---------------------------------------|
| Accessory material: | Polycarbonate, glass-fibre reinforced |
|---------------------|---------------------------------------|