

Flange

GFL 394-m

GFL 394-m

Flange

Productnumber: 07239401

Dimensions: 275 x 15 x 119 mm

Flange "metric" equipped, 2 x flange connectors (GFV)

with 30x KVR M16 (unequipped)

IP65



Technical Data

electrical characteristics

Type of protection:	IP65
UL Type Rating:	not specified

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	275 mm
Length:	15 mm
Height:	119 mm

Material characteristics

UV-resistant:	no
Industry quality:	yes

mechanical properties

with cable restraint:	no
-----------------------	----

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Polycarbonate, glass-fibre reinforced
---------------------	---------------------------------------