

Flange

GFL 421-m

GFL 421-m

Flange

Productnumber: 07242101

Dimensions: 395 x 119 x 15 mm

Flange with metric knockouts, 2 x flange connectors (GFV)

Knockouts for cable insertions: 1x M50/M40, 2x M40/M32, 8x M25/M20

IP65



Technical Data

electrical characteristics

Type of protection:	IP65
UL Type Rating:	3R

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	395 mm
Length:	119 mm
Height:	15 mm

Material characteristics

UV-resistant:	yes
Industry quality:	yes

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Polycarbonate, glass-fibre reinforced
---------------------	---------------------------------------

Accessories

[26344001 - BEL Air M40 - Ventilation element set](#)