

Busbar terminal

## SKL 024



### SKL 024

#### Busbar terminal

Productnumber: 07502401

Dimensions: 32 x 30 x 115 mm

Busbar terminal, for rails 12 x 5 mm / 12 x 10 mm,  
for aluminium and copper conductors

**for AL/CU conductors 1x (35-50)re, 1x  
(35-240)rm, 1x (50-185)se, 1x (35-240)sm**

240<sup>2</sup>

## Technical Data

### electrical characteristics

Max. conductor cross section:	240 mm <sup>2</sup>
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	16 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (max):	50 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (min):	16 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (max):	150 mm <sup>2</sup>

### Dimensions

Width:	32 mm
Length:	30 mm
Height:	115 mm

### Material characteristics

Industry quality:	no
-------------------	----

### mechanical properties

Connection 1: Tightening moment:	20 Nm
----------------------------------	-------