


Busbar terminal

## SKL 092



### SKL 092

#### Busbar terminal

Productnumber: 07509201

Dimensions: 30 x 36 x 106 mm

Busbar terminal, for rails 12 x 5 mm / 12 x 10 mm,  
for aluminium and copper conductors

**for AL/CU conductors 1x (25-50)re, 1x  
(25-150)rm, 1x (50-150)se, 1x (35-150)sm, 2x  
(25-50)re, 2x (25-70)rm, 2x (50-70)se, 2x  
(35-70)sm**

## Technical Data

### electrical characteristics

Max. conductor cross section:	185 mm <sup>2</sup>
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	25 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (max):	185 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (min):	25 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (max):	185 mm <sup>2</sup>

### Dimensions

Width:	30 mm
Length:	36 mm
Height:	106 mm

### Material characteristics

Industry quality:	no
-------------------	----

### mechanical properties

Connection 1: Tightening moment:	40 Nm
----------------------------------	-------