

Busbar terminal

SKL 118



SKL 118

Busbar terminal

Productnumber: 07511801

Dimensions: 28,5 x 29 x 53 mm

Busbar terminal, for copper rails 12/20/25/30 x 10 mm

for CU conductor 1x (50-185mm²) re/rm/sm/rf+AE

Technical Data

electrical characteristics

Max. conductor cross section:	185 mm ²
Rated current:	500 A
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	0
Connection 1: Connectable conductor cross-section, single-wire (min):	50 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	185 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	16 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	185 mm ²

Dimensions

Width:	28.5 mm
Length:	29 mm
Height:	53 mm

Material characteristics

Industry quality:	no
-------------------	----

mechanical properties

Connection 1: Tightening moment:	20 Nm
----------------------------------	-------