


Busbar terminal

SKL 570



SKL 570

Busbar terminal

Productnumber: 07557001

Dimensions: 20,5 x 28 x 39 mm

Bus bar terminals for copper rails 12/20/25/30 x 5 mm

Connection for Cu 16-70 mm²

70²

Technical Data

electrical characteristics

Max. conductor cross section:	70 mm ²
Rated current:	400 A
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	0
Connection 1: Connectable conductor cross-section, single-wire (min):	16 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	70 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	16 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	70 mm ²

Dimensions

Width:	20.5 mm
Length:	28 mm
Height:	39 mm

Material characteristics

Industry quality:	no
-------------------	----

mechanical properties

Connection 1: Tightening moment:	8 Nm
----------------------------------	------