

Direct terminal clamp

KU 1



KU 1

Direct terminal clamp

Productnumber: 07611001

Dimensions: 70 x 45 x 32 mm

Direct terminal, universal, for aluminium and copper conductors, from KU 250 also for laminated flat cable

Direct terminal M10 for conductors, 50-90se, 35-70sm, 16-50re, 10-50re

Technical Data

electrical characteristics

| | |
|---|--------------------|
| shockproof: | No |
| Connection 1: Connection type: | Screws |
| Connection 1: Suitable for Cu conductors: | 1 |
| Connection 1: Suitable for Al conductors: | 1 |
| Connection 1: Connectable conductor cross-section, single-wire (min): | 16 mm ² |
| Connection 1: Connectable conductor cross-section, single-wire (max): | 95 mm ² |
| Connection 1: Connectable conductor cross-section, stranded (min): | 10 mm ² |
| Connection 1: Connectable conductor cross-section, stranded (max): | 70 mm ² |

Dimensions

| | |
|---------|-------|
| Width: | 70 mm |
| Length: | 45 mm |
| Height: | 32 mm |

Material characteristics

| | |
|-------------------|----|
| Industry quality: | no |
|-------------------|----|

mechanical properties

| | |
|----------------------------------|-------|
| Connection 1: Tightening moment: | 22 Nm |
|----------------------------------|-------|