

Busbar terminal

SKLAL 116

SKLAL 116

Busbar terminal

Productnumber: 07611601

Dimensions: 12 x 25,5 x 31,5 mm

Busbar terminal, for copper rails 12/20/25/30 x 10 mm

for connection of AL/CU conductors 1.5-16mm²



16²

Technical Data

electrical characteristics

Max. conductor cross section:	16 mm ²
Rated current:	180 A
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	1.5 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	16 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	1.5 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	16 mm ²

Dimensions

Width:	12 mm
Length:	25.5 mm
Height:	31.5 mm

Material characteristics

Industry quality:	no
-------------------	----

mechanical properties

Connection 1: Tightening moment:	3 Nm
----------------------------------	------