

Direct terminal clamp

KU 2



KU 2

Direct terminal clamp

Productnumber: 07612001

Dimensions: 80 x 65 x 40 mm

Direct terminal, universal, for aluminium and copper conductors, from KU 250 also for laminated flat cable

Direct terminal M12 for conductors, 50-240se, 50-185sm, 35-70re, 35-50re

Technical Data

electrical characteristics

shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	35 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	240 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	10 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	185 mm ²

Dimensions

Width:	80 mm
Length:	65 mm
Height:	40 mm

Material characteristics

Industry quality:	no
-------------------	----

mechanical properties

Connection 1: Tightening moment:	22 Nm
----------------------------------	-------