

Busbar terminal

SKLAL 135

SKLAL 135

Busbar terminal

Productnumber: 07613501

Dimensions: 16 x 26,5 x 36 mm

Busbar terminal, for copper rails 12/20/25/30 x 10 mm

for connection of AL/CU conductors 4-35mm²



35²

Technical Data

electrical characteristics

Max. conductor cross section:	35 mm ²
Rated current:	270 A
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	4 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	35 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	4 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	35 mm ²

Dimensions

Width:	16 mm
Length:	26.5 mm
Height:	36 mm

Material characteristics

Industry quality:	no
-------------------	----

mechanical properties

Connection 1: Tightening moment:	6 Nm
----------------------------------	------