

Busbar terminal

## SKLAL 170

### SKLAL 170

**Busbar terminal**

Productnumber: 07617001

Dimensions: 20,5 x 28 x 45 mm

Busbar terminal, for copper rails 12/20/25/30 x 10 mm

**for connection of AL/CU conductors 16-70mm<sup>2</sup>**



70°

## Technical Data

### electrical characteristics

Max. conductor cross section:	70 mm <sup>2</sup>
Rated current:	400 A
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	16 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (max):	70 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (min):	16 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (max):	120 mm <sup>2</sup>

### Dimensions

Width:	20.5 mm
Length:	28 mm
Height:	45 mm

### Material characteristics

Industry quality:	no
-------------------	----

### mechanical properties

Connection 1: Tightening moment:	12 Nm
----------------------------------	-------