

Direct terminal clamp

## KU 400



### KU 400

**Direct terminal clamp**

Productnumber: 07640001

Dimensions: 170 x 120 x 40 mm

Direct terminal, universal, for aluminium and copper conductors, from KU 250 also for laminated flat cable

**Direct terminal M10 for conductors, 50-240 mm<sup>2</sup> (flexible up to 300 mm<sup>2</sup>), 16-95 mm<sup>2</sup> and laminated flat copper 22 x 13 mm, for load break switch GTE 440**

## Technical Data

### electrical characteristics

shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	50 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (max):	300 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (min):	50 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (max):	240 mm <sup>2</sup>

### Dimensions

Width:	170 mm
Length:	120 mm
Height:	40 mm

### Material characteristics

Industry quality:	no
-------------------	----