

Direct terminal clamp

KU 630



KU 630

Direct terminal clamp

Productnumber: 07663001

Dimensions: 170 x 120 x 40 mm

Direct terminal, universal, for aluminium and copper conductors, from KU 250 also for laminated flat cable

Direct terminal M12 for conductors, 70-300 mm² and laminated flat copper, 34 x 20 mm, for load break switch GTE 463

Technical Data

electrical characteristics

shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	70 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	300 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	70 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	300 mm ²

Dimensions

Width:	170 mm
Length:	120 mm
Height:	40 mm

Material characteristics

Industry quality:	no
-------------------	----