

Empty enclosure

AL 88-6



AL 88-6

Empty enclosure

CUSTOMIZABLE

Productnumber: 15000501

Dimensions: 80 x 75 x 57 mm

Empty enclosure, protection class IP66, Aluminium, powder-coated painting, internal fixing points, for installations in industrial environments and protected outdoor areas

Box: Aluminium, powder-coated painting, Lid: Aluminium, powder-coated painting, silver-grey, smooth sidewalls

IP66

IK09



Technical Data

electrical characteristics

Type of protection:	IP66
UL Type Rating:	not specified

Colours

Cover colour:	silver-grey
---------------	-------------

Dimensions

Width:	80 mm
Length:	75 mm
Height:	57 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Industry quality:	yes

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK09
Cover screw torque:	2.5 Nm
Stackable:	no
Type of top part:	Cover
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	75 °C
24h ambient temperature:	60 °C

Ambient conditions

Installation location:	protected outdoor areas
Location:	Installations in industrial environments and protected outdoor areas

Material

Base unit material:	Aluminium, powder-coated painting
Cover material:	Aluminium, powder-coated painting
Sealing material:	Polyurethane

Accessories

[15400401 - AL ALS-kl - External attachment set](#)

[15500501 - AL MPS-88 - Mounting plate](#)