

Empty enclosure

## AL 1010-8



### AL 1010-8

Empty enclosure

CUSTOMIZABLE

Productnumber: 15000801

Dimensions: 100 x 100 x 81 mm

Empty enclosure, protection class IP66, Aluminium, powder-coated painting, internal fixing points, for installations in industrial environments and protected outdoor areas

**Box: Aluminium, powder-coated painting, Lid: Aluminium, powder-coated painting, silver-grey, smooth sidewalls**

IP66

IK09



## Technical Data

### electrical characteristics

Type of protection:	IP66
UL Type Rating:	not specified

### Colours

Cover colour:	silver-grey
---------------	-------------

### Dimensions

Width:	100 mm
Length:	100 mm
Height:	81 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Industry quality:	yes

### mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK09
Cover screw torque:	2.5 Nm
Stackable:	no
Type of top part:	Cover
Fastening:	internal fixing points

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	75 °C
24h ambient temperature:	60 °C

### Ambient conditions

Installation location:	protected outdoor areas
Location:	Installations in industrial environments and protected outdoor areas

### Material

Base unit material:	Aluminium, powder-coated painting
Cover material:	Aluminium, powder-coated painting
Sealing material:	Polyurethane

## Accessories

[15400401 - AL ALS-kl - External attachment set](#)

[15421001 - AL ASS - External hinge set](#)

[15500801 - AL MPS-1010 - Mounting plate](#)