

Empty enclosure

AL 3323-11



AL 3323-11

Empty enclosure

CUSTOMIZABLE

Productnumber: 15001601

Dimensions: 330 x 230 x 111 mm

Empty enclosure, protection class IP66, Aluminium, powder-coated painting, internal fixing points, for installations in industrial environments and protected outdoor areas

Box: Aluminium, powder-coated painting, Lid: Aluminium, powder-coated painting, silver-grey, smooth sidewalls

IP66

IK09



Technical Data

electrical characteristics

Type of protection:	IP66
UL Type Rating:	not specified

Colours

Cover colour:	silver-grey
---------------	-------------

Dimensions

Width:	330 mm
Length:	230 mm
Height:	111 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Industry quality:	yes

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK09
Cover screw torque:	2.5 Nm
Stackable:	no
Type of top part:	Cover
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	75 °C
24h ambient temperature:	60 °C

Ambient conditions

Installation location:	protected outdoor areas
Location:	Installations in industrial environments and protected outdoor areas

Material

Base unit material:	Aluminium, powder-coated painting
Cover material:	Aluminium, powder-coated painting
Sealing material:	Polyurethane

Accessories

[15400601 - AL ALS-gro - External attachment set](#)

[15421001 - AL ASS - External hinge set](#)

[15501601 - AL MPS-3323 - Mounting plate](#)

[16201601 - AL NS35-316 - Standard rail](#)