

Empty enclosure

## ALS 3927-12

### ALS 3927-12

Empty enclosure

Productnumber: 15101201

Dimensions: 388 x 270 x 117 mm

Empty enclosure, protection class IP66, Aluminium, powder-coated painting, certified by UL (UL 50 & CSA 22.2 No. 94.1-07, UL 50E & CSA C22.2 No. 94.2-07), for installations in industrial environments and protected outdoor areas

**Box: Aluminium, powder-coated painting, Lid: Aluminium, powder-coated painting, silver-grey, smooth sidewalls**



Internal dimensions and mounting points correspond to the respective TK PS/PC dimension

## Technical Data

### electrical characteristics

Protection class:	I
Type of protection:	IP66
vented:	no
UL Type Rating:	4X, 12

### Colours

Cover colour:	silver-grey
---------------	-------------

### Dimensions

Width:	388 mm
Length:	270 mm
Height:	117 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Industry quality:	yes

### mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK09
Flange variant:	no
Stackable:	no
Type of top part:	Cover

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	75 °C

### Ambient conditions

24h ambient temperature:	60 °C
Installation location:	protected outdoor areas
Location:	Installations in industrial environments and protected outdoor areas

### Material

Base unit material:	Aluminium, powder-coated painting
Cover material:	Aluminium, powder-coated painting
Sealing material:	Silicone

### Certificates

Test mark:	UL (UL 50 & CSA 22.2 No. 94.1-07, UL 50E & CSA C22.2 No. 94.2-07)
------------	---

## Accessories

[15400601 - AL ALS-gro - External attachment set](#)

[15421001 - AL ASS - External hinge set](#)

[19501201 - TK MPI-3625 - Mounting plate](#)

[19701201 - TK MPS-3625 - Mounting plate](#)

[19821601 - NS 35-216 - Standard rail](#)

[19833601 - NS 35-336 - Standard rail](#)