

Empty enclosure

## TG PC 88-6-to



### TG PC 88-6-to

Empty enclosure

CUSTOMIZABLE

Productnumber: 20100301

Dimensions: 84 x 82 x 55 mm

Empty enclosure, protection class IP66/IP67, Polycarbonate, certified by UL (UL 508 & CSA C22.2 No. 14-13, UL 50 & CSA 22.2 No. 94.1-7 & UL 50E & CSA C22.2 No. 94.2-7), DLG (Ammonia resistance),  $U_i=690V$  AC,  $U_i=1000V$  DC, internal fixing points, for installation in industrial environments and protected outdoor areas, with quick release

**Box: Polycarbonate, grey, Lid: Polycarbonate, transparent, smooth sidewalls**

**Accessories supplied:**

**Cover retainer, 4 fastening screws for accessories**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Protection class:	II
Type of protection:	IP66/IP67
UL Type Rating:	12

### Colours

Base unit colour:	grey
Cover colour:	transparent

### Dimensions

Width:	84 mm
Length:	82 mm
Height:	55 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Stackable:	yes
Type of top part:	Cover
Fastening:	internal fixing points

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas
Location:	Installations in industrial environments and protected outdoor areas

### Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

### Certificates

Test mark:	UL (UL 508 & CSA C22.2 No. 14-13, UL 50 & CSA 22.2 No. 94.1-7 & UL 50E & CSA C22.2 No. 94.2-7)
Test mark:	DLG (Ammonia resistance)

## Accessories

[89601101 - MABF 65-2 - Mast/pipe fixing set](#)

[18200201 - TG ABL - External fixing lugs kit](#)

[18200401 - TG PST1 - Sealing kit](#)

[18200601 - TG DVS-42 - Cover retainer](#)

[18600301 - TG MPI-88 - Mounting plate](#)

[18700301 - TG MPS-88 - Mounting plate](#)

[19599501 - LFR - Stepped drill](#)

[19706901 - TS 15-66 - Standard rail](#)

[19806801 - NS 35-66 - Standard rail](#)

[26241201 - DAE M12 - Pressure balance element](#)