

Twist plug

WST M20



WST M20

Twist plug

Productnumber: 20342001

Dimensions: 24 x 24 x 20 mm

Twist plug, IP54, M₂₀ x 1.5 mm, with closed sealing membrane, grey

Sealing range 8 - 13,5 mm, Thread length 12 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	24 mm
--------	-------

Length:	24 mm
---------	-------

Height:	20 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for wall thickness max:	9 mm
-------------------------	------

for sealing range min:	8 mm
------------------------	------

for sealing range max:	13.5 mm
------------------------	---------

for wall thickness min:	1 mm
-------------------------	------

Ambient conditions

Installation location:	Indoors
------------------------	---------
