

Twist plug

WST M25



WST M25

Twist plug

Productnumber: 20342501

Dimensions: 29,5 x 29,5 x 22 mm

Twist plug, IP54, M_ x 1.5 mm, with closed sealing membrane, grey

Sealing range 9 - 16 mm, Thread length 12 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	29.5 mm
--------	---------

Length:	29.5 mm
---------	---------

Height:	22 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for wall thickness max:	11 mm
-------------------------	-------

for sealing range min:	9 mm
------------------------	------

for sealing range max:	16 mm
------------------------	-------

for wall thickness min:	1 mm
-------------------------	------

Ambient conditions

Installation location:	Indoors
------------------------	---------
