

Twist plug

WST M40

WST M40

Twist plug

Productnumber: 20344001

Dimensions: 45,8 x 45,8 x 28 mm

Twist plug, IP54, M_ x 1.5 mm, with closed sealing membrane, grey

Sealing range 17 - 24 mm, Thread length 14 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	45.8 mm
--------	---------

Length:	45.8 mm
---------	---------

Height:	28 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for wall thickness max:	11 mm
-------------------------	-------

for sealing range min:	17 mm
------------------------	-------

for sealing range max:	24 mm
------------------------	-------

for wall thickness min:	1 mm
-------------------------	------

Ambient conditions

Installation location:	Indoors
------------------------	---------
