

Twist plug

WST M63



WST M63

Twist plug

Productnumber: 20346301

Dimensions: 68,8 x 68,8 x 37 mm

Twist plug, IP54, M₆₃ x 1.5 mm, with closed sealing membrane, grey

Sealing range 24 - 43 mm, Thread length 20 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	68.8 mm
Length:	68.8 mm
Height:	37 mm

Material characteristics

UV-resistant:	no
Halogen free:	yes
Industry quality:	no

mechanical properties

for wall thickness max:	17 mm
for sealing range min:	24 mm
for sealing range max:	43 mm
for wall thickness min:	1 mm

Ambient conditions

Installation location:	Indoors
------------------------	---------