

Twist nipple

## WNI M16/sw



### WNI M16/sw

**Twist nipple**

Productnumber: 21301601

Dimensions: 19,8 x 19,8 x 17 mm

Twist nipple, IP54, M<sub>16</sub> x 1.5 mm with open sealing membrane, polyethylene, black

**Sealing range 5 - 10 mm, Thread length 9 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP54
---------------------	------

---

### Colours

---

Accessory colour:	deep black
-------------------	------------

---

### Dimensions

---

Width:	19.8 mm
--------	---------

---

Length:	19.8 mm
---------	---------

---

Height:	17 mm
---------	-------

---

### Material characteristics

---

UV-resistant:	no
---------------	----

---

Halogen free:	yes
---------------	-----

---

Flammability class according with UL94:	HB
---	----

---

Glow-wire flammability according to EN 60695-2-11:	650 °C
--	--------

---

Industry quality:	no
-------------------	----

---

### mechanical properties

---

for wall thickness max:	8 mm
-------------------------	------

---

for sealing range min:	5 mm
------------------------	------

---

for sealing range max:	10 mm
------------------------	-------

---

for wall thickness min:	1 mm
-------------------------	------

---

### Ambient conditions

---

Installation location:	Indoors
------------------------	---------

---