

Twist nipple

WNI M16



WNI M16

Twist nipple

Productnumber: 21341601

Dimensions: 19,8 x 19,8 x 17 mm

Twist nipple, IP54, M₁₆ x 1.5 mm with open sealing membrane, polyethylene, grey

Sealing range 5 - 10 mm, Thread length 9 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	19.8 mm
--------	---------

Length:	19.8 mm
---------	---------

Height:	17 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	HB
---	----

Glow-wire flammability according to EN 60695-2-11:	650 °C
--	--------

Industry quality:	no
-------------------	----

mechanical properties

for wall thickness max:	8 mm
-------------------------	------

for sealing range min:	5 mm
------------------------	------

for sealing range max:	10 mm
------------------------	-------

for wall thickness min:	1 mm
-------------------------	------

Ambient conditions

Installation location:	Indoors
------------------------	---------
