

Twist nipple

## WNI M25



### WNI M25

#### Twist nipple

Productnumber: 21342501

Dimensions: 29,5 x 29,5 x 22 mm

Twist nipple, IP54, M<sub>12</sub> x 1.5 mm with open sealing membrane, polyethylene, grey

**Sealing range 9 - 16 mm, Thread length 12 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP54
---------------------	------

---

### Colours

---

Accessory colour:	light grey
-------------------	------------

---

### Dimensions

---

Width:	29.5 mm
--------	---------

---

Length:	29.5 mm
---------	---------

---

Height:	22 mm
---------	-------

---

### Material characteristics

---

UV-resistant:	no
---------------	----

---

Halogen free:	yes
---------------	-----

---

Flammability class according with UL94:	HB
---	----

---

Glow-wire flammability according to EN 60695-2-11:	650 °C
--	--------

---

Industry quality:	no
-------------------	----

---

### mechanical properties

---

for wall thickness max:	11 mm
-------------------------	-------

---

for sealing range min:	9 mm
------------------------	------

---

for sealing range max:	16 mm
------------------------	-------

---

for wall thickness min:	1 mm
-------------------------	------

---

### Ambient conditions

---

Installation location:	Indoors
------------------------	---------

---