

Twist nipple

WNI M32



WNI M32

Twist nipple

Productnumber: 21343201

Dimensions: 37,5 x 37,5 x 25 mm

Twist nipple, IP54, M₃ x 1.5 mm with open sealing membrane, polyethylene, grey

Sealing range 11 - 22 mm, Thread length 14 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	37.5 mm
--------	---------

Length:	37.5 mm
---------	---------

Height:	25 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	HB
---	----

Glow-wire flammability according to EN 60695-2-11:	650 °C
--	--------

Industry quality:	no
-------------------	----

mechanical properties

for wall thickness max:	11 mm
-------------------------	-------

for sealing range min:	11 mm
------------------------	-------

for sealing range max:	22 mm
------------------------	-------

for wall thickness min:	1 mm
-------------------------	------

Ambient conditions

Installation location:	Indoors
------------------------	---------
