

Stepped nipple

## **SNI M20**

### **SNI M20**

#### **Stepped nipple**

Productnumber: 21642001

Dimensions: 25 x 25 x 17 mm

Stepped nipple, IP55, with closed sealing membrane, can be cut into multiple steps, thermoplastic elastomer (TPE), grey, for wall thicknesses from 1.5 - 4 mm

#### **Sealing range 5 - 16 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP55
---------------------	------

---

### Colours

---

Accessory colour:	light grey
-------------------	------------

---

### Dimensions

---

Width:	25 mm
--------	-------

---

Length:	25 mm
---------	-------

---

Height:	17 mm
---------	-------

---

### Material characteristics

---

UV-resistant:	no
---------------	----

---

Halogen free:	yes
---------------	-----

---

Industry quality:	no
-------------------	----

---

### mechanical properties

---

for wall thickness max:	4.5 mm
-------------------------	--------

---

for sealing range min:	5 mm
------------------------	------

---

for sealing range max:	16 mm
------------------------	-------

---

for wall thickness min:	1.5 mm
-------------------------	--------

---

### Ambient conditions

---

Installation location:	Indoors
------------------------	---------

---