

Stepped nipple

SNI M40

SNI M40

Stepped nipple

Productnumber: 21644001

Dimensions: 45 x 45 x 24 mm

Stepped nipple, IP55, with closed sealing membrane, can be cut into multiple steps, thermoplastic elastomer (TPE), grey, for wall thicknesses from 1.5 - 4 mm

Sealing range 14 - 54 mm



Technical Data

electrical characteristics

Type of protection:	IP55
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	45 mm
--------	-------

Length:	45 mm
---------	-------

Height:	24 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for wall thickness max:	4.5 mm
-------------------------	--------

for sealing range min:	13 mm
------------------------	-------

for sealing range max:	34.0 mm
------------------------	---------

for wall thickness min:	1.5 mm
-------------------------	--------

Ambient conditions

Installation location:	Indoors
------------------------	---------
