

Cable gland

## **KVR M20-MGM/sw**

### **KVR M20-MGM/sw**

#### **Cable gland**

Productnumber: 22702001

Dimensions: 26,5 x 26,5 x 36 mm

Cable gland, IP68, with strain relief, polyamide, M\_ x 1.5 mm, with locknut, black

**Sealing range 6 - 12 mm, Thread length 9 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP68
---------------------	------

---

### Colours

---

Accessory colour:	deep black
-------------------	------------

---

### Dimensions

---

Width:	26.5 mm
--------	---------

---

Length:	26.5 mm
---------	---------

---

Height:	36 mm
---------	-------

---

Nominal size:	M20
---------------	-----

---

### Material characteristics

---

UV-resistant:	yes
---------------	-----

---

Halogen free:	yes
---------------	-----

---

Flammability class according with UL94:	V2
---	----

---

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

---

Industry quality:	yes
-------------------	-----

---

### mechanical properties

---

for sealing range min:	6 mm
------------------------	------

---

for sealing range max:	12 mm
------------------------	-------

---

### Ambient conditions

---

Installation location:	unprotected outdoor areas
------------------------	---------------------------

---

### Material

---

Accessory material:	Polyamide
---------------------	-----------

---