

Cable gland

## **KVR M32-MGM/sw**

### **KVR M32-MGM/sw**

#### **Cable gland**

Productnumber: 22703201

Dimensions: 40 x 40 x 50 mm

Cable gland, IP68, with strain relief, polyamide, M\_ x 1.5 mm, with locknut, black

**Sealing range 11 - 21 mm, Thread length 11 mm**



---

## Technical Data

### electrical characteristics

---

|                     |      |
|---------------------|------|
| Type of protection: | IP68 |
|---------------------|------|

---

### Colours

---

|                   |            |
|-------------------|------------|
| Accessory colour: | deep black |
|-------------------|------------|

---

### Dimensions

---

|        |       |
|--------|-------|
| Width: | 40 mm |
|--------|-------|

---

|         |       |
|---------|-------|
| Length: | 40 mm |
|---------|-------|

---

|         |       |
|---------|-------|
| Height: | 50 mm |
|---------|-------|

---

|               |     |
|---------------|-----|
| Nominal size: | M32 |
|---------------|-----|

---

### Material characteristics

---

|               |     |
|---------------|-----|
| UV-resistant: | yes |
|---------------|-----|

---

|               |     |
|---------------|-----|
| Halogen free: | yes |
|---------------|-----|

---

|                                         |    |
|-----------------------------------------|----|
| Flammability class according with UL94: | V2 |
|-----------------------------------------|----|

---

|                                                    |        |
|----------------------------------------------------|--------|
| Glow-wire flammability according to EN 60695-2-11: | 850 °C |
|----------------------------------------------------|--------|

---

|                   |     |
|-------------------|-----|
| Industry quality: | yes |
|-------------------|-----|

---

### mechanical properties

---

|                        |       |
|------------------------|-------|
| for sealing range min: | 11 mm |
|------------------------|-------|

---

|                        |       |
|------------------------|-------|
| for sealing range max: | 21 mm |
|------------------------|-------|

---

### Ambient conditions

---

|                        |                           |
|------------------------|---------------------------|
| Installation location: | unprotected outdoor areas |
|------------------------|---------------------------|

---

### Material

---

|                     |           |
|---------------------|-----------|
| Accessory material: | Polyamide |
|---------------------|-----------|

---