

Cable gland

KVR M50-MGM/sw

KVR M50-MGM/sw

Cable gland

Productnumber: 22705001

Dimensions: 60 x 60 x 63 mm

Cable gland, IP68, with strain relief, polyamide, M_ x 1.5 mm, with locknut, black

Sealing range 21 - 34,5 mm, Thread length 13 mm



Technical Data

electrical characteristics

Type of protection:	IP68
---------------------	------

Colours

Accessory colour:	deep black
-------------------	------------

Dimensions

Width:	60 mm
Length:	60 mm
Height:	63 mm
Nominal size:	M50

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	yes

mechanical properties

for sealing range min:	27 mm
for sealing range max:	34.5 mm

Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

Material

Accessory material:	Polyamide
---------------------	-----------
