

Cable gland

## **KVR M16-MGM**

### **KVR M16-MGM**

#### **Cable gland**

Productnumber: 22741601

Dimensions: 22 x 22 x 31 mm

Cable gland, IP68, with strain relief, polyamide, M\_ x 1.5 mm, with locknut, grey

**Sealing range 4 - 10 mm, Thread length 8 mm**



---

## Technical Data

### electrical characteristics

Type of protection:	IP68
---------------------	------

---

### Colours

Accessory colour:	light grey
-------------------	------------

---

### Dimensions

Width:	22 mm
--------	-------

---

Length:	22 mm
---------	-------

---

Height:	31 mm
---------	-------

---

Nominal size:	M16
---------------	-----

---

### Material characteristics

UV-resistant:	yes
---------------	-----

---

Halogen free:	yes
---------------	-----

---

Flammability class according with UL94:	V2
---	----

---

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

---

Industry quality:	yes
-------------------	-----

---

### mechanical properties

for sealing range min:	4 mm
------------------------	------

---

for sealing range max:	10.0 mm
------------------------	---------

---

Type of accessory:	other
--------------------	-------

---

### Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

---

### Material

Accessory material:	Polyamide
---------------------	-----------

---