

Cable gland

KVR M40-MGM

KVR M40-MGM

Cable gland

Productnumber: 22744001

Dimensions: 50 x 50 x 54 mm

Cable gland, IP68, with strain relief, polyamide, M_ x 1.5 mm, with locknut, grey

Sealing range 16 - 28 mm, Thread length 11 mm



Technical Data

electrical characteristics

Type of protection:	IP68
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	50 mm
--------	-------

Length:	50 mm
---------	-------

Height:	54 mm
---------	-------

Nominal size:	M40
---------------	-----

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

Industry quality:	yes
-------------------	-----

mechanical properties

for sealing range min:	16 mm
------------------------	-------

for sealing range max:	28.0 mm
------------------------	---------

Type of accessory:	other
--------------------	-------

Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

Material

Accessory material:	Polyamide
---------------------	-----------
