

Cable gland

## KVR M50-MGM

### KVR M50-MGM

#### Cable gland

Productnumber: 22745001

Dimensions: 60 x 60 x 63 mm

Cable gland, IP68, with strain relief, polyamide, M\_ x 1.5 mm, with locknut, grey

**Sealing range 21 - 34,5 mm, Thread length 13 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP68
---------------------	------

---

### Colours

---

Accessory colour:	light grey
-------------------	------------

---

### Dimensions

---

Width:	60 mm
--------	-------

---

Length:	60 mm
---------	-------

---

Height:	63 mm
---------	-------

---

Nominal size:	M50
---------------	-----

---

### Material characteristics

---

UV-resistant:	yes
---------------	-----

---

Halogen free:	yes
---------------	-----

---

Flammability class according with UL94:	V2
---	----

---

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

---

Industry quality:	yes
-------------------	-----

---

### mechanical properties

---

for sealing range min:	27 mm
------------------------	-------

---

for sealing range max:	34.5 mm
------------------------	---------

---

Type of accessory:	other
--------------------	-------

---

### Ambient conditions

---

Installation location:	unprotected outdoor areas
------------------------	---------------------------

---

### Material

---

Accessory material:	Polyamide
---------------------	-----------

---