

Cable gland

KVR M25-MGM/or



KVR M25-MGM/or

Cable gland

Productnumber: 22762501

Dimensions: 31,5 x 31,5 x 44 mm

Cable gland, IP68, with strain relief, polyamide, M_ x 1.5 mm, with locknut, orange

Sealing range 9 - 16 mm, Thread length 11 mm



Technical Data

electrical characteristics

| | |
|---------------------|------|
| Type of protection: | IP68 |
|---------------------|------|

Colours

| | |
|-------------------|------------|
| Accessory colour: | reinorange |
|-------------------|------------|

Dimensions

| | |
|--------|---------|
| Width: | 31.5 mm |
|--------|---------|

| | |
|---------|---------|
| Length: | 31.5 mm |
|---------|---------|

| | |
|---------|-------|
| Height: | 44 mm |
|---------|-------|

| | |
|---------------|-----|
| Nominal size: | M25 |
|---------------|-----|

Material characteristics

| | |
|---------------|-----|
| UV-resistant: | yes |
|---------------|-----|

| | |
|---------------|-----|
| Halogen free: | yes |
|---------------|-----|

| | |
|---|----|
| Flammability class according with UL94: | V2 |
|---|----|

| | |
|--|--------|
| Glow-wire flammability according to EN 60695-2-11: | 850 °C |
|--|--------|

| | |
|-------------------|-----|
| Industry quality: | yes |
|-------------------|-----|

mechanical properties

| | |
|------------------------|------|
| for sealing range min: | 9 mm |
|------------------------|------|

| | |
|------------------------|-------|
| for sealing range max: | 16 mm |
|------------------------|-------|

Ambient conditions

| | |
|------------------------|---------------------------|
| Installation location: | unprotected outdoor areas |
|------------------------|---------------------------|
