

Cable gland

KVR M40 LG-MGM/sw

KVR M40 LG-MGM/sw

Cable gland

Productnumber: 22904001

Dimensions: 50 x 50 x 61 mm

Cable gland, IP68, with strain relief, long thread, M₂₀ x 1.5 mm, with locknut, polyamide, black

Sealing range 16 - 28 mm, Thread length 18 mm



Technical Data

electrical characteristics

Type of protection:	IP68
---------------------	------

Colours

Accessory colour:	deep black
-------------------	------------

Dimensions

Width:	50 mm
Length:	50 mm
Height:	61 mm
Nominal size:	M40

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	yes

mechanical properties

for sealing range min:	16 mm
for sealing range max:	28 mm

Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

Material

Accessory material:	Polyamide
---------------------	-----------
