

Attachment bushes

## AST M20



### AST M20

#### Attachment bushes

Productnumber: 23042001

Dimensions: 24,5 x 24,5 x 22,5 mm

Mounting socket IP55, with open sealing membrane, thermoplastic elastomer (TPE), for wall thicknesses from 1.5 - 4.0 mm, grey

**Sealing range 8 - 13,5 mm**



---

## Technical Data

### electrical characteristics

Type of protection:	IP55
---------------------	------

---

### Colours

Accessory colour:	light grey
-------------------	------------

---

### Dimensions

Width:	24.5 mm
--------	---------

---

Length:	24.5 mm
---------	---------

---

Height:	22.5 mm
---------	---------

---

Nominal size:	M20
---------------	-----

---

### Material characteristics

UV-resistant:	no
---------------	----

---

Halogen free:	yes
---------------	-----

---

Flammability class according with UL94:	HB
---	----

---

Glow-wire flammability according to EN 60695-2-11:	650 °C
--	--------

---

Industry quality:	no
-------------------	----

---

### mechanical properties

for sealing range min:	8 mm
------------------------	------

---

for sealing range max:	13.5 mm
------------------------	---------

---

### Ambient conditions

Installation location:	Indoors
------------------------	---------

---