

Attachment bushes

AST M25



AST M25

Attachment bushes

Productnumber: 23042501

Dimensions: 29,5 x 29,5 x 22,6 mm

Mounting socket IP55, with open sealing membrane, thermoplastic elastomer (TPE), for wall thicknesses from 1.5 - 4.0 mm, grey

Sealing range 9 - 18,5 mm



Technical Data

electrical characteristics

Type of protection:	IP55
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	29.5 mm
--------	---------

Length:	29.5 mm
---------	---------

Height:	22.6 mm
---------	---------

Nominal size:	M25
---------------	-----

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	HB
-----------------------------------------	----

Glow-wire flammability according to EN 60695-2-11:	650 °C
----------------------------------------------------	--------

Industry quality:	no
-------------------	----

mechanical properties

for sealing range min:	9 mm
------------------------	------

for sealing range max:	18.5 mm
------------------------	---------

Ambient conditions

Installation location:	Indoors
------------------------	---------
