

Sealing plugs

VST M16

VST M16

Sealing plugs

Productnumber: 23141601

Dimensions: 20,5 x 20,5 x 13,5 mm

Sealing plugs, IP55, with closed sealing membrane, thermoplastic elastomer (TPE), for wall thickness 1.5 - 4.0 mm, for sealing of metric enclosure apertures that are not required, grey

Sealing range 6 - 10 mm



Technical Data

electrical characteristics

Type of protection:	IP55
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	20.5 mm
--------	---------

Length:	20.5 mm
---------	---------

Height:	13.5 mm
---------	---------

Material characteristics

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for sealing range min:	6 mm
------------------------	------

for sealing range max:	10 mm
------------------------	-------

Ambient conditions

Installation location:	Indoors
------------------------	---------
