

Cable gland

## **KVR M20**



### **KVR M20**

#### **Cable gland**

Productnumber: 24742001

Dimensions: 30 x 30 x 36 mm

Cable gland, IP68, with strain relief, polyamide, M\_ x 1.5 mm, without locknut, grey

**Sealing range 6 - 12 mm, Thread length 9 mm**



## Technical Data

### electrical characteristics

Type of protection:	IP68
---------------------	------

### Colours

Accessory colour:	light grey
-------------------	------------

### Dimensions

Width:	30 mm
--------	-------

Length:	30 mm
---------	-------

Height:	36 mm
---------	-------

Nominal size:	M20
---------------	-----

### Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

Industry quality:	yes
-------------------	-----

### mechanical properties

for sealing range min:	6 mm
------------------------	------

for sealing range max:	12 mm
------------------------	-------

### Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

### Material

Accessory material:	Polyamide
---------------------	-----------