

Cable gland

KVR M20-GDB



KVR M20-GDB

Cable gland

Productnumber: 24742101

Dimensions: 30 x 30 x 37 mm

Cable gland, IP68, with strain relief, polyamide, M_ x 1.5 mm, without locknut, grey

Sealing range 7 - 14 mm, Thread length 9 mm



Technical Data

electrical characteristics

Type of protection:	IP68
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	30 mm
--------	-------

Length:	30 mm
---------	-------

Height:	37 mm
---------	-------

Nominal size:	M20
---------------	-----

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

Industry quality:	yes
-------------------	-----

mechanical properties

for sealing range min:	7 mm
------------------------	------

for sealing range max:	14 mm
------------------------	-------

Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

Material

Accessory material:	Polyamide
---------------------	-----------
