

Cable gland

KVR M25 LG



KVR M25 LG

Cable gland

Productnumber: 24842501

Dimensions: 31,2 x 31,2 x 48 mm

Cable gland, IP68, with strain relief, long thread, M_ x 1.5 mm, without locknut, polyamide, grey

Sealing range 9 - 16 mm, Thread length 15 mm



Technical Data

electrical characteristics

Type of protection:	IP68
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	31.2 mm
--------	---------

Length:	31.2 mm
---------	---------

Height:	48 mm
---------	-------

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

Industry quality:	yes
-------------------	-----

mechanical properties

for sealing range min:	9 mm
------------------------	------

for sealing range max:	16 mm
------------------------	-------

Ambient conditions

Installation location:	unprotected outdoor areas
------------------------	---------------------------

Material

Accessory material:	Polyamide
---------------------	-----------
