

Double-membrane seals

DMS M16/sw



DMS M16/sw

Double-membrane seals

Productnumber: 26001601

Dimensions: 20,7 x 20,7 x 13,2 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, black

Sealing range 5 - 9 mm



Technical Data

electrical characteristics

Type of protection:	IP66
---------------------	------

Colours

Accessory colour:	deep black
-------------------	------------

Dimensions

Width:	20.7 mm
--------	---------

Length:	20.7 mm
---------	---------

Height:	13.2 mm
---------	---------

Nominal size:	M16
---------------	-----

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for sealing range min:	5 mm
------------------------	------

for sealing range max:	9 mm
------------------------	------

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Rubber
---------------------	--------
